



SHINING 3D
DENTAL

FabCure 2 Post-curing Unit

Fabulous Curing



SHINING3DDENTAL.COM



FabCure 2

Post-curing Unit

FabCure 2 is recommended as the standard post-curing tool for 3D printers from Shining3D. With FabCure 2, each resin cure profile is finely tuned to bring the part to its peak performance through precise heat and light. FabCure 2 precisely defines the post-processing steps of the printed object to ensure high precision and optimal material performance, while automating the process.

SHINING3D

High Power Multi-surface Light Curing


From the sides and bottom, 30 multi-directional LEDs emit powerful UV light that instantly penetrates deep into the surface of the part, completely curing the printed object within a few minutes. With a power of 70W, these LEDs provide a high power curing cycle, ensuring an efficient curing process.

30

multi-directional LEDs

60°C

precisely controls ambient
temperatures




Rapid Chamber Heating

The ceramic heating module is integrated with multiple temperature sensors. The chamber heats up quickly to 60 degrees, contributing to the enhancement of mechanical and flexural properties. The FabCure 2 heating system precisely controls ambient temperatures to 60 °C.



Customized Curing Parameter

FabCure 2 provides optimal curing parameters for Shining3D resins, which can be updated via the wireless network. Customized curing parameter settings are supported.



Larger Curing Volume

Curing volume up to $\Phi 210\text{mm}$ and H180mm supports a wide range of dental appliances.

Smart Material Library

With the most up-to-date cloud-based smart material library, the FabCure 2 is always synchronized. The FabCure 2 is equipped with Wi-Fi which enables over-the-air updates to deploy the latest firmware and configurations. Your device learns from our process engineering experts all the time.



Easy Operation with OLED Screen

The popular convenient control knob is integrated into an OLED screen enabling an interactive and convenient operation experience.



TECHNICAL SPECIFICATION

FabCure 2

Dimension (W x D x H)	290mm × 290mm × 367.5mm
Weight	10.5kg
Curing volume	Φ210mm H180mm
Operating temperature	10~30℃
Max. Curing temperature	60℃
Light source	UV LED
Wavelength	385nm ~ 405nm
LED power	70W
Power	AC 100~240V, 150W
Interface	WI-FI

Notice: SHINING 3D reserves the right to explain any alteration of the specifications and pictures.



📍 1102 Embassy Chambers, 3rd Road, Khar West, Mumbai - 400052, India
☎ +91 22 6127 7777 📞 +919930006127 ✉ sales@nkpatelandsons.com
🌐 www.nkpatelandsons.com 📺 @nkpatelandsons 📷 /nkpatelandsons

SHINING 3D
DENTAL

sales@shining3d.com
www.shining3ddental.com